

CHEMTRONICS®

Technical Data Sheet

TDS # CP410

Optic Prep™ Presaturated Wipe

PRODUCT DESCRIPTION

Optic Prep™ Presaturated Wipes are high quality premoistened lens-grade tissues for cleaning optical surfaces. These highly effective cleaning wipes are ideal for cleaning and polishing optical surfaces, lenses, photographic equipment, CRT screens and instruments. Optic Prep™ is safe for use on Fiber Optic Connectors.

Optic Prep™ Presaturated Wipes contain ultra-pure isopropyl alcohol (65% IPA / 35% Pure Water) on an ultra-soft, lens-grade tissue.

- Plastic Safe
- Dries Fast
- Leaves No Residue
- Nonabrasive
- Upper Ozone Safe; CFC/HCFC Free

TYPICAL APPLICATIONS

Optic Prep™ Presaturated Wipes cleans:

- Plastic and glass lenses
- Machine optics and alignment lenses
- Fiber Optic Connectors
- CRT's
- Microscopes
- Copier optics and prisms
- Mirrors

TYPICAL PRODUCT DATA AND PHYSICAL PROPERTIES

Specific Gravity	0.87
Solubility in Water	Soluble
Evaporation Rate (Ether = 1)	<1
Appearance	Clear, Colorless Liquid
Flash Point (TCC)	72° F
Percent Volatile	100%
Shelf life	2 years
RoHS/WEEE Status	

COMPATIBILITY

Optic Prep™ Presaturated Wipes are generally compatible with most plastics, glass and metals. As with any chemical product, component compatibility must be determined on a non-critical area prior to use. Check compatibility with all non-glare coatings.

<u>Material</u>	<u>Compatibility</u>
Aluminum	Excellent
Buna-N	Good
CPVC	Excellent
Epoxy	Excellent
Neoprene	Good
Noryl [®]	Excellent
Phenolic	Excellent
Cross-Linked PE	Good
Polycarbonate	Good
Polypropylene	Good
Polystyrene	Fair
PVC	Good
Teflon [™]	Excellent
Tygon [™]	Good
Viton [™]	Excellent

ENVIRONMENTAL IMPACT DATA

ENVIRONMENTAL IMPACT DATA			
CFC	0.0%	VOC	65%
HCFC	0.0%	HFC	0.0%
CL Solv.	0.0%	ODP	0.0

CFC, HCFC, CL. SOLV., VOC, and HFC numbers shown are the content by weight. Ozone depletion potential (ODP) is determined in accordance with the Montreal Protocol and U.S. Clean Air Act of 1990. The ODP of this product is zero.

NOTE:

This information is believed to be accurate. It is intended for professional end users having the skills to evaluate and use the data properly. ITW CHEMTRONICS[®] does not guarantee the accuracy of the data and assumes no liability in connection with damages incurred while using it.

Chemtronics[®] is a registered trademark of ITW Chemtronics. All rights reserved. Optic Prep[™] is a trademark of ITW Chemtronics. All rights reserved.

MANUFACTURED BY:
ITW CHEMTRONICS
8125 COBB CENTER DRIVE
KENNESAW, GA 30152
1-770-424-4888 REV. (06/06)

AVAILABILITY

CP410 50 Premoistened Wipes

USAGE INSTRUCTIONS

For industrial use only.
Read MSDS carefully prior to use.
Remove wipe from packets and lightly wipe away any dust or contaminants from surfaces.
Allow surface to dry completely before use.

TECHNICAL & APPLICATION ASSISTANCE

ITW Chemtronics[®] provides a technical hotline to answer your technical and application related questions. Call toll free at: **1-800-TECH-401.**

<u>DISTRIBUTED BY:</u>